



4" Smart Valve Cut Sheet

Materials

Acetron GP

Stainless Steel

Aluminum (flange – no water or pipe contact)

FDA approved internal o-rings

Certifications

NSF 61 (potable water)

NSF 372 (lead free)

Certifying laboratory: IAPMO R&T



Installation Dimensions

4" SMART VALVE:

| | |
|--------------------------------|---------------|
| Body Length – Flange to Flange | 8.05" |
| Approximate Weight | 15 lbs |
| Bolt Pattern | Standard |
| Bolt Holes | Through Holes |
| Shipping Weight | 16 lbs |

For best results install the Smart Valve downstream of water meter and backflow preventer (if present), but before any other equipment such as a pressure reducer or booster pump. Where *possible* it is recommended (but not critical) to have 10 diameters of pipe between the water meter and the valve. All flanged installations to use gaskets at each flange.

IMPORTANT: If the pipe the Smart Valve is being installed in is used as a Ground Fault Line, The Smart Valve will NOT conduct a current through the pipe without a grounding strap. As a precaution, ALWAYS use a ground strap across the valve from pipe to pipe.